

SatPax® ValuSeal® 1500

Pre-wetted Sealed Edge Cleanroom Laundered 100% Polyester Knit Wiper

SatPax® ValuSeal® 1500 combines ValuSeal® 1500 sealed edge cleanroom laundered wipers composed of 100% continuous filament polyester knit fabric with various concentrations of isopropyl alcohol.

This pre-wetted format provides a cost effective and easy to use solution versus traditional bulk handling of solvents, maintenance of squirt bottles and inconsistent wetting and cleaning associated with wetting a dry wiper.



Key Attributes

- 100% continuous filament polyester knit
- Laser sealed edge for reduced fiber contamination
- Laundered and packaged in Berkshire's ISO Class 4 cleanroom
- Pre-wetted with consistent IPA/ DI Water concentrations and saturation levels
- Re-sealable solvent resistant packaging

Benefits

- Critically low particles, fibers, ions and extractables
- High abrasion resistance
- Reduces alcohol usage and preparation / handling costs
- Reduces VOC emissions
- Increases cleaning efficiency
- Increases cleaning protocol consistency

Environmental

- Reduces VOC (Volatile Organic Compound) emissions
- Light weight material design can reduce landfill waste impact when compared to more traditional heavier weight products
- Flatpack packaging reduces packaging waste by 28% compared to j-folded packaging.
- Complies with RoHS and pre-registered under REACH

Applications

- Designed for use in ISO Class 3 and higher cleanroom environments
- Designed for use in wet cleaning of critical surfaces where control of flammable solvents and flammable solvent concentrations is required

Packing Options

Available in 30 sheets j-folded pack or 50 sheet flat pack formats.

Alcohol Mixtures

Alcohol / DI Water mixtures can be varied to fit the customer requirements. Typical mixtures are 70/30 and 9/91 IPA/DI Water.

Saturation Levels

The amount of solution contained in each wiper can be varied according to customer requirements. Higher saturation levels apply more solution to the surface during cleaning.

Sterile Validated Option

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10⁻⁶

Other Class 3 and above Pre-wetted wipers

- SatPax® 3000
- SatPax® HA-R

www.berkshire.com

Contact: Tel 1 800 242 7000 / 1 413 528 2602
 info@berkshire.com

Americas	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp

Technical Data (In Dry State)

Attribute		Units	Value	Test Method
Basis Weight		g/m ²	130	TAPPI T-410
Caliper		µm	473	TAPPI T-411
Fibers	≥100µm	fibers/cm ²	0.037	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.2
Particles	≥0.5µm	x10 ³ /cm ²	0.74	IEST-RP.CC004.3, Sec 6.1.3 / Sec 6.2.1
Sorbency	Capacity	mL/m ²	538	IEST-RP.CC004.3, Sec 8.1 modified / Sec 8.2 modified
	Efficiency	mL/g	4.1	
	Rate	seconds	1	
Non-Volatile Residue	DI Water	g/m ²	0.0031	IEST-RP.CC004.3, Sec 7.1.2
	IPA	g/m ²	0.0065	
Ions	Na ⁺	ppm	0.069	IEST-RP.CC004.3, Sec 7.2.2
	K ⁺	ppm	0.016	
	Ca ⁺⁺	ppm	0.041	
	Mg ⁺⁺	ppm	0.0088	
	Cl ⁻	ppm	0.21	

Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request

Order Information:

Product	Number	Size	Shts/pk	Pks/cs	IPA/DI	Saturation	VOC % by	Style
SatPax® VS1500	SPXV1500.001.12	9x9" (23x23cm)	30	12	70/30	33%	35%	J-fold
SatPax® VS1500	SPXV1500.004.12	9x9" (23x23cm)	30	12	6/94	33%	2.7%	J-fold

Other Berkshire Products




Wipers




Glove Liners



Mop Systems



Documentation Systems



Face Masks



Swabs